



GLPOLY XK-S65 Two-Component Thermal Gap filler Two-component Silicone Thermally Conductive Gel

Description	Key Features	Typical Applications
XK-S65 two-component thermal gap filler cures at room temperature or elevated heat, thixotropic featuring high performance and superior softness. It deflects at low compressive forces and accommodates a variety of different gap thickness. It is a perfect solution for fragile components with high topography or tolerances It is compatible with automated dispense processes and in place of thermal gap pad.	Thermal conductivity 6.5W/m.K Fast cured by heating Conforming, ideal for delicate component and low stress applications Cure at room or elevated temperature 100% solid, no cure by-product	Computer& peripherals Automotive electronics Telecommunication Anti-shock Between any heat-generating semiconductor and a heat sink

Material Properties

	XK-S65	METHOD	Unit	
Color / Part A	White	Visual		
Color / Part B	blue	Visual		
Features	Soft GEL			
Density	3.4±0.1	ASTM D792	g/cm3	
Before-Cured Property				
A:B	1:1			
Mixed Viscosity @ 25℃	750±50	ASTM D2196	Pa.s	
Shelf Life @ 25℃	6 months			
After Cured Property				
Color	blue	Visual		
Cure Schedule 1	6hr/25℃	ASTM D4473 10%/90% hardness measurement	hours	
Cure Schedule 2	40min/80°C	ASTM D4473 10%/90% hardness measurement	min	
Cure Schedule 3	10min/100℃	ASTM D4473 10%/90% hardness measurement	min	
Working time	120 min/25℃	ASTM D4473 10%/90% hardness measurement	min	
Hardness	Shore 00 70±5	ASTM D2240	Shore 00	
Tensile Strength.	0.1±0.05	ASTM D412	Мра	

Elongation	>20	ASTM D412	%	
Service Temp	-60~200	ASTM G 166	${\mathbb C}$	
Siloxane Volatile s D4~D20	<0.01	GC-FID	%	
Electrical Property				
Dielectric strength	>10	ASTM D149	KV/mm	
Volume resistivity	>10 ¹³	ASTM D257	Ohm-cm	
Dielectric Constant	8	ASTM D150	(1KHz)	
Flame Rating	V-0	UL94		
Thermal Property				
Thermal Conductivity	6.5	ASTM D5470	W/m*K	
Heat Capacity	1	ASTM E1269	J/g-K	



Operating Procedures & Recommendation:

- 1. The ratio of AB is 1:1, and the two doses of AB glue should be mixed evenly.
- 2. Option& Tools: automatic dispensing machine or manual feeding gun.
- 3. The curing time is related to the amount of dispensing thickness of finished product. Take 1.0mm thickness as an example:

Curing temperature °C	Curing time
25	6-24 hr
50	60~120min
80	40~60min
100	10~20min
150	1~3 min

Storage Method

- 1. Storage mode: it can be stored for 6 months at room temperature below 25 degrees before mixed.
- 2. The AB component should be used up once after mixing, and it cannot be kept for further use

Caution:

Contact Surface:

If the contact surface meet with sulfur, phosphorus, nitrogen and organic metal salt and other substances, it will prevent the hardening of the surface, slightly it may resist to the hardening of the surface and contact surface, seriously it may cause no hardening permanently and completely.

Environment Aspects:

In addition to the requirements of the correct mixing ratio, While in the use of mixing containers ,such as paper cups, plastic cups ,because of inner wall of the container contain oil wax, penetration of plasticizers inside plastic , baking epoxy resin and varnish inside the oven, it will be contaminated Therefore, please clean and dry the machine before use, especially to avoid the possibility of contact with the above substances,please do the test first.

Packing:

4 Standard Packing Editions as Following:

1st Edition: 25+25ml AB component, 6 layers *10 pcs, total 60pcs, standard carton size 37.2*30.8*22.5cm

2nd Edition: 200+200ml AB component, 2layers *6pcs, total 12pcs, standard carton size 51.5*38.5*13.5Ccm

3rd Edition: 20L+20L Bucket packing

4th Edition: 200L +200L Bucket packing



Learn More

For additional information or Material Safety Data Sheets on the complete line of GLPOLY thermal interface management solutions, please call our office

tel: 86-755-27579310, visit www. glpoly.com or send a message to **kemmy@glpoly.com**.

LIMITED WARRANTY INFORMATION – PLEASE READ CAREFULLY

The information contained herein is offered in good faith and is believed to be accurate. However, because conditions and methods of use of our products are beyond our control, this information should not be used in substitution for customer's tests to ensure that our products are safe, effective, and fully satisfactory for the intended end use. Suggestions of use shall not be taken as inducements to infringe any patent.

GLPOLY 's sole warranty is that our products will meet the sales specifications in effect at the time of shipment.

Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted.

GLPOLY SPECIFICALLY DISCLAIMS ANY OTHER EXPRESS OR IMPLIED WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE OR MERCHANTABILITY.

GLPOLY DISCLAIMS ANY LIABILITY FOR ANY INCIDENTAL OR CONSEQUENTIAL DAMAGES.

GLPOLY is a registered trademark of Goldlink Tongda Corporation. ©2008, Goldlink Tongda Corporation.. All rights reserved.

